

Suction Cup Fittings (With Pads)

Standard / Deep Type

Suction Cup Fittings (With Pads) / Suction Cup Units

Small Type

Fixed Type Up: One-Touch (Shape K)

Type	Accessory	Pad Shape	MPad Material
MVPKN	VPNT	Standard	Nitrile Rubber
MVPKE	VPUE	Standard	Conductive Silicon Rubber
MVPKF	VPUF	Standard	Fluoro Rubber
MVFKN	VPFT	Deep	Nitrile Rubber
MVFKF	VPFF	Deep	Fluoro Rubber

Standard and Deep Type No.2-8 No.10-40

Dimensions in () are for Ø2 ~ 4.

Fitting Material: Brass Surface Treatment: Electroless Nickel Plating

Spring Type Up: One-Touch (Shape T)

Type	Accessory	Pad Shape	MPad Material
MVPTN	VPNT	Standard	Nitrile Rubber
MVPTU	VPUE	Standard	Conductive Silicon Rubber
MVPTF	VPUF	Standard	Fluoro Rubber
MVFTN	VPFT	Deep	Nitrile Rubber
MVFTF	VPFF	Deep	Fluoro Rubber

Standard and Deep Type No.2-8 No.10-40

Dimensions in () are for Ø2 ~ 4.

Fitting Material: Brass Surface Treatment: Electroless Nickel Plating

Part Number	Shape K		Unit Price												
	Type	Pad Material	No.	1 ~ 50 pcs(s)											
MVPK (Standard)	NEF	2	4	2	4	28.3	6	10	8	2	M6x0.75	6			
		3	4	3	4	28.3	6	10	8	2	M6x0.75	6			
		4	4	4	4	28.3	6	10	8	2	M6x0.75	6			
		6	6	7	32.6	9.5	12	12	3	M10x1.0	12.5				
		8	6	8	5.5	31.1	8	12	12	3	M10x1.0	12.5			
		10	6	10	8	34.1	12	18.5	14	4	M12x1.0	21			
		15	6	15	9	35.1	13	18.5	14	4	M12x1.0	21.5			
		20	6	20	10	37.7	15.6	18	17	4	M14x1.0	36.5			
		For orders larger than indicated quantity, please check with WOS.													

Part Number	Shape T		Unit Price												
	Type	Pad Material	No.	1 ~ 50 pcs(s)											
MVPT (Standard)	NEF	2	4	2	4	43.2	17.5	17							
		3	4	3	4	43.2	17.5	17							
		4	4	4	4	43.2	17.5	17							
		6	6	6	7	43.2	19.5	18.5							
		8	6	8	5.5	45.6	18	18.5							
		10	6	10	8	60.1	26	35.5							
		15	6	15	9	61.1	27	36							
		20	6	20	10	62.1	28	39.5							
		For orders larger than indicated quantity, please check with WOS.													

Spring Type Side: One-Touch (Shape L)

Type	Accessory	Pad Shape	MPad Material
MVPLN	VPNT	Standard	Nitrile Rubber
MVPLE	VPUE	Standard	Conductive Silicon Rubber
MVPLF	VPUF	Standard	Fluoro Rubber
MVFLN	VPFT	Deep	Nitrile Rubber
MVFLF	VPFF	Deep	Fluoro Rubber

Standard and Deep Type No.2-8 No.10-40

Dimensions in () are for Ø2 ~ 4.

Fitting Material: Brass Surface Treatment: Electroless Nickel Plating

Direct-Mount Spring Type Screw (Shape S)

Type	Accessory	Pad Shape	MPad Material
MVPSN	VPNT	Standard	Nitrile Rubber
MVPSU	VPUE	Standard	Conductive Silicon Rubber
MVPSF	VPUF	Standard	Fluoro Rubber
MVFSN	VPFT	Deep	Nitrile Rubber
MVFSF	VPFF	Deep	Fluoro Rubber

Standard and Deep Type No.2-8 No.10-40

Dimensions in () are for Ø2 ~ 4.

Fitting Material: Brass Surface Treatment: Electroless Nickel Plating

Part Number	Shape L		Unit Price												
	Type	Pad Material	No.	1 ~ 30 pcs(s)											
MVPL (Standard)	NEF	2	4	2	4	16.7	12.5	13.5							
		3	4	3	4	16.7	12.5	13.5							
		4	4	4	4	16.7	12.5	13.5							
		6	6	7	4	25	18.1	13	15.5						
		8	6	8	5.5	39.5	23.5	18.1	13	15.5					
		10	6	10	8	58.1	35	20.1	18.5	47.5					
		15	6	15	9	59.1	36	20.1	18.5	48					
		20	6	20	10	60.1	37	20.1	18.5	51.5					
		For orders larger than indicated quantity, please check with WOS.													

Part Number	Shape S		Unit Price												
	Type	Pad Material	No.	1 ~ 30 pcs(s)											
MVPS (Standard)	TFM	2	4	2	4	9.5	32	22.5	14.5						
		3	4	3	4	9.5	32	22.5	14.5						
		4	4	4	4	9.5	32	22.5	14.5						
		6	6	7	4	10.1	35	23.5	15.5						
		8	6	8	5.5	10.1	35	23.5	15.5						
		10	6	10	8	11.7	51	39.3	55.5						
		15	6	15	9	11.7	52	40.3	56						
		20	6	20	10	11.7	54	42.3	58.5						
		For orders larger than indicated quantity, please check with WOS.													

Spring Type Long Stroke (Shape R)

Type	Accessory	Pad Shape	MPad Material
MVPRN	VPNT	Standard	Nitrile Rubber
MVPRE	VPUE	Standard	Conductive Silicon Rubber
MVPRF	VPUF	Standard	Fluoro Rubber
MVFRN	VPFT	Deep	Nitrile Rubber
MVFRF	VPFF	Deep	Fluoro Rubber

Standard and Deep Type No.4-8 No.10-40

Dimensions in () are for Ø2 ~ 4.

Fitting Material: Brass Surface Treatment: Electroless Nickel Plating

Spring Type Long Stroke (Shape R)

Part Number	Shape R		Unit Price												
	Type	Pad Material	No.	1 ~ 20 pcs(s)											
MVPR (Standard)	NEF	4	4	4	4	57.2	27	17.5	20.5	0.6~1.7					
		6	4	6	7	56.7	26.5	17.5	20	0.8~2.7					
		8	4	8	5.5	55.2	25	17.5	20	0.8~2.7					
		10	6	10	8	64.6	30.5	20	36.5	2.0~5.2					
		15	6	15	9	65.6	31.5	20	37	2.0~5.2					
		20	6	20	10	68.1	34	20	42	3.3~10.0					
		For orders larger than indicated quantity, please check with WOS.													

Direct Mounting Type Small (Shape J)

Type	Accessory	Pad Shape	MPad Material
MVPJN	VPJN	Small	Nitrile Rubber
MVPJS	VPJS	Small	Conductive Silicon Rubber
MVPJF	VPJF	Small	Fluoro Rubber

Standard Type is suitable for suction on flat workpiece.
Deep Type is suitable for suction on round objects.

Applicable spherical surface size list for deep type suction cups

Spherical diameter: S (mm)	20	25	30	40
Applicable Pad Size: Ø (mm)	20	25	30	40

Part Number	Unit Price		
	Type	Pad Material	
MVPJ (Small)	NSF	0.7	0.7
		1.5	1.5
		2	2
		4	4

Structure Diagram

Suction Cup Units

Type	Material	Pad Shape	Hardness	Color
VPNT	Nitrile Rubber	Standard	Shore A50 ~ 60	Black
VPUE	Conductive Silicon Rubber	Standard	Shore A60	Black
VPUF	Fluoro Rubber	Standard	Shore A50 ~ 60	Gray
VPFT	Nitrile Rubber	Deep	Shore A50 ~ 60	Black
VPJN	Fluoro Rubber	Deep	Shore A50 ~ 60	Black
VPJS	Nitrile Rubber	Small	Shore A55	Black
VPJF	Fluoro Rubber	Small	Shore A60	Black

Standard Type

Deep Type

Small Type

Part Number	Applicable Vacuum Fitting No.	Mounting	VPNT		VPUE		VPUF	
			Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
2	2	Insertion Type	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
3	3		1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
4	4		1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
6	6		1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
8	8	Recessed Type	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
10	10		1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
15	15		1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20
20	20	Attachment Type	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20	1-9 pcs(s)	10-20

Type	VPNT, VPFT, VPJN		VPUE, VPJS		VPUF, VPFF, VPJF	
	Max. Operating Temp.	Min. Operating Temp.	Max. Operating Temp.	Min. Operating Temp.	Max. Operating Temp.	Min. Operating Temp.
Weather Resistance	△	○	△	○	△	○
Ozone Resistance	△	○	△	○	△	○
Acid Resistance	△	○	△	○	△	○
Alkali Resistance	△	○	△	○	△	○
Oil Resistance (Gasoline, Light Oil)	○	○	△	○	△	○
Oil Resistance (Benzene, Toluene)	△	○	△	○	△	○
Surface Resistivity	10 ¹⁰ ~10 ¹² /sq		10 ¹⁰ ~10 ¹² /sq		10 ¹⁰ ~10 ¹² /sq	

Characteristic Data

Standard and Deep Type

For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number: MVPKN4 VPFF30